

Getting The Right Gasket is as easy as A B C

Ask us for a **TRG Sample Kit.** Use the color code here to identify the correct profile.

A. Identify the Profile

How does your gasket mount to the door?




Is it a **Dart Style**? (TRG color code: Black)

Has a narrow arrow

Does it **Push In**? (TRG color code: Green

Has a wide wedge



Dart style **Glass Door** gaskets are in a separate group for easy identification. (TRG color code: Red)

www.Facebook.com/TRGaskets www.Twitter.com/TRGaskets

B. Measure your gasket

All gaskets can be measured Corner-to-Corner (Outside Dimensions). Look for "Measure Here" on each profile diagram.



Dart-style and **Push-In** gaskets can also be measured Dart-to-Dart If a gasket is ill-fitting, in poor condition, or missing, we recommend Dart-to-Dart measurement.



A simple way to be sure of getting an accurate measurement is to measure from the center of the grooves, or from the outside of one side to the inside of the other (see below).



C. Number of Sides

Most **Walk-in gaskets** do not extend across the bottom of the door. Tell us if your gasket has 3 or 4 sides.

Still confused? Check our **Total Pages** in the back of this catalog, where our items are listed by manufacturer.

Total Refrigeration Gaskets Call us at 1.800.452.4275